

**DATASHEET** 

# HZ102 / HZ202 SUPERCAPACITOR

Revision 4.6. June 2020

# **Electrical Specifications**

The HZ102 is a single cell supercapacitor. The HZ202 is a dual cell supercapacitor with two HZ102 cells in series, so HZ202 capacitance = Capacitance of HZ102/2 and HZ202 ESR =  $2 \times HZ102 = 2 \times HZ1$ 

**Table 1: Absolute Maximum Ratings** 

Parameter	Name		Conditions	Min	Typical	Max	Units
Terminal	Vpeak	HZ102		0		2.9	V
Voltage		HZ202				5.8	
Temperature <sup>1</sup>	Tmax			-40		+85	°C

#### **Table 2: Electrical Characteristics**

Parameter	Name		Conditions	Min	Typical	Max	Units
Terminal Voltage	Vn	HZ102		0		2.75	V
		HZ202		0		5.5	
Capacitance	С	HZ102	DC, 23°C	136	170	204	- mF
		HZ202		72	90	108	
ESR	ESR	HZ102	DC, 23°C		90	108	mΩ
		HZ202			175	210	
Leakage Current	lι		2.75V, 23°C 120hrs		1	2	μΑ
RMS Current	I <sub>RMS</sub>		23°C			5	Α
Peak Current <sup>2</sup>	lР		23°C			30	Α

 $<sup>^{1}</sup>$ Max continuous operating temp = +70 $^{\circ}$ C but can withstand excursions to +85 $^{\circ}$ C.

#### **Table 3: Thickness**

HZ102F		No adhesive tape on underside of the supercapacitor	HZ102G	_	Adhesive tape on underside, release tape removed
HZ202F	2.5mm		HZ202G	2.6mm	

This datasheet should be read in conjunction with the <u>CAP-XX Supercapacitor Product Guide</u> which contains information common to our product lines.

<sup>&</sup>lt;sup>2</sup>Non-repetitive current, single pulse to discharge fully charged supercapacitor.



#### **Definition of Terms**

In its simplest form, the Equivalent Series Resistance (ESR) of a capacitor is the real part of the complex impedance. In the time domain, it can be found by applying a step discharge current to a charged cell as in Fig. 1. In this figure, the supercapacitor is pre-charged and then discharged with a current pulse, I =1A for duration 0.01 secs.




Figure 1: Effective capacitance, instantaneous capacitance and ESR for an HZ202

The ESR is found by dividing the instantaneous voltage step ( $\Delta V$ ) by I. In this example = (4.96V-4.80V)/1.02A = 157m $\Omega$ .

The instantaneous capacitance (C<sub>i</sub>) can be found by taking the inverse of the derivative of the voltage, and multiplying it by I.

The effective capacitance for a pulse of duration  $\Delta t_n$ ,  $Ce(\Delta t_n)$  is found by dividing the total charge removed from the capacitor  $(\Delta Q_n)$  by the voltage lost by the capacitor  $(\Delta V_n)$ . For constant current  $Ce(\Delta t_n) = I \times \Delta t_n/\Delta V_n$ . Ce increases as the pulse width increases and tends to the DC capacitance value as the pulse width becomes very long (~10 secs). After 2msecs, Fig 1 shows the voltage drop  $V_{2ms} = (4.80V - 4.682 \text{ V}) = 118\text{mV}$ . Therefore  $Ce(2ms) = 1.02\text{A} \times 2\text{ms}/118\text{mV} = 17.2\text{mF}$ . After 10ms, the voltage drop = 4.80V - 4.529V = 271mV. Therefore  $Ce(10ms) = 1.02\text{A} \times 100\text{ms}/271\text{mV} = 37.6\text{mF}$ . The DC capacitance of an HZ202 = 90mF. Note that  $\Delta V$ , or IR drop, is not included because very little charge is removed from the capacitor during this time. Ce shows the time response of the capacitor and it is useful for predicting circuit behaviour in pulsed applications.



## **Measurement of DC Capacitance**




Fig 2: Measurement of DC Capacitance for an HZ202

Fig 2 shows the measurement of DC capacitance by drawing a constant 100mA current from a fully charged supercapacitor and measuring the time taken to discharge from 1.5V to 0.5V for a single cell, or from 3V to 1V for a dual cell supercapacitor. In this case,  $C = 0.1A \times 1.89s / 2V = 94.5mF$ , which is well within the 90mF +/- 20% tolerance for an HZ202 cell.

#### Measurement of ESR




Fig 3: Measurement of ESR for an HZ202

Fig 3 shows DC measurement of ESR by applying a step load current to the supercapacitor and measuring the resulting voltage drop. CAP-XX waits for a delay of 50 $\mu$ s after the step current is applied to ensure the voltage and current have settled. In this case the ESR is measured as  $163.1 \text{mV}/1.04 \text{A} = 156.8 \text{m}\Omega$ .



## **Effective Capacitance**




Figure 4: Effective Capacitance

Fig 4 shows the effective capacitance for the HZ102, HZ202 @ 23°C. This shows that for a 1msec PW, you will measure 10% of DC capacitance or 17mF for an HZ102 or 9mF for an HZ202. At 10msecs you will measure 32% of the DC capacitance, and at 100msecs you will measure 70% of DC capacitance. Ceffective is a time domain representation of the supercapacitor's frequency response. If, for example, you were calculating the voltage drop if the supercapacitor was supporting 1A for 10msecs, then you would use the Ceff(10msecs) = 32% of DC capacitance = 28.8mF for an HZ202, so Vdrop = 1A x ESR + 1A x duration/C = 1A x 175m $\Omega$  + 1A x 10ms / 28.8mF = 522.2mV. The next section on pulse response shows how the effective capacitance is sufficient for even short pulse widths.

#### **Pulse Response**




Fig 5 shows that the HZ202 supercapacitor does an excellent job supporting a GPRS class 10 pulse train, drawing 1.8A for 1.1ms at 25% duty cycle. The source is current limited to 0.6A and the supercapacitor provides the 1.2A difference to achieve the peak current. At first glance the freq response of Fig 8 indicates the supercapacitor would not support a 1ms pulse, but the Ceff of 11mF coupled with the low ESR supports this pulse train with only ~330mV droop in the supply rail.

Fig 5: HZ202 Pulse Response with GPRS Class 10 Pulse Train



# DC Capacitance variation with temperature




Fig 6: Capacitance change with temperature

Fig 6 shows that DC capacitance is approximately constant with temperature.

# **ESR** variation with temperature




Fig 7: ESR change with temperature

Fig 7 shows that ESR at -40°C is  $\sim$ 2.6 x ESR at room temp, and that ESR at 80°C is  $\sim$ 0.8 x ESR at room temperature.



# **Frequency Response**




Fig 8: Frequency Response of Impedance (biased at 2.5V with a 50mV test signal)




Fig 9: Frequency Response of ESR, Capacitance & Inductance

Fig 8 shows the supercapacitor behaves as an ideal capacitor until approx 5 Hz when the magnitude no longer rolls off proportionally to 1/freq and the phase crosses -45°. Performance of supercapacitors with frequency is complex and the best predictor of performance is Fig 4 showing effective capacitance as a function of pulsewidth.



## **Leakage Current**




Fig 10: Leakage Current

Fig 10 shows the leakage current for HZ102 at room temperature. The leakage current decays over time and the equilibrium value leakage current will be reached after ~120hrs at room temperature. The typical equilibrium leakage current is 1µA at room temperature. At 70°C leakage current will be ~10µA.

### **Charge Current**




Fig 11: Charging an HZ102 with low current

The corollary to the slow decay in leakage currents shown in Fig 10 is that charging a supercapacitor at very low currents takes longer than theory predicts. At higher charge currents, the charge rate is as theory predicts. For example, it should take 180mF x 2.4V / 0.00002A = 6hrs to charge a 180mF supercapacitor to 2.4V at 20µA, but Fig 11 shows it took 54hrs. At 200µA charging occurs at a rate close to the theoretical rate.



#### **RMS Current**




Fig 12: Temperature rise in HZ202 with RMS current

Continuous current flow into/out of the supercapacitor will cause self-heating, which limits the maximum continuous current the supercapacitor can handle. This is measured by a current square wave with 50% duty cycle, charging the supercapacitor to rated voltage at a constant current, and then discharging the supercapacitor to half rated voltage at the same constant current value. For a square wave with 50% duty cycle, the RMS current is the same as the current amplitude. Fig 12 shows the increase in temperature as a function of RMS current. From this, the maximum RMS current in an application can be calculated, for example, if the ambient temperature is 40°C, and the maximum desired temperature for the supercapacitor is 70°C, then the maximum RMS current should be limited to 2.5A, which causes a 30°C temperature increase.

# **CAP-XX Supercapacitors Product Guide**

Refer to the package drawings in the <u>CAP-XX Supercapacitors Product Guide</u> for detailed information of the product's dimensions, PCB landing placements, active areas and electrical connections, as well for information on endurance and shelf life, transportation and storage, assembly and soldering, safety and RoHS/REACH certification.